

**TABLE 1 — Falk Oil Seal Part Numbers – Sizes 2070 thru 2195 ★**

DRIVE SIZE	No. of Reductions	High Speed Seal No.	Low Speed Seal No.
2070	2	912753	912741 †
	3	912747	912741 †
	4	912743	912741
2080	2	912754	912760 †
	3	912747	912760 †
	4	912743	912760
2090	2	912754	912761
	3	912749	912761
	4	912743	912761
2100	2	912757	912762 †
	3	912749	912762 †
	4	912743	912762
2110	2	912757	912763
	3	912753	912763
	4	912743	912763
2120 2125	2	912758	912764
	3	912753	912764
	4	912747	912764
2130 2135	2	912759	912765 †
	3	912754	912765 †
	4	912747	912765
2140 2145	2	912741	912766
	3	912754	912766
2150 2155	2	912760	912767
	3	912757	912767
2160 2165	2	912761	912769
	3	912757	912769
2170 2175	2	912762	912769
	3	912758	912769
2180 2185	2	912762 ‡ & 912763	912770
	3	912759	912770
2190 2195	2	912763 ‡ & 912764	912771
	3	912741	912771

★ YBX drives are double and triple reduction only.

† For YBX drives with low speed shaft DOWN, seal numbers are as follows: Size 2070 = 912761; 2080 = 912762; 2100 = 912763; 2130 &amp; 2135 = 912742.

‡ 4.13 H.S. Ratio only.

**TABLE 2 — Falk Oil Seal Part Numbers – Sizes 50 thru 175**

DRIVE SIZE	No. of Reductions	High Speed Seal No.	Low Speed Seal No.
50	2	912745	912757
	3	912743	912757
60	2	912749	912758
	3	912743	912758
70	2	912753	912741
	3	912745	912741
80	2	912754	912760
	3	912745	912760
90	2	912754	912761
	3	912749	912761
100	2	912757	912762
	3	912749	912762
110	2	912757	Ext. Up 912763
	3	912753	912763
120	2	912757	Ext. Down 912764
	3	912753	912764
130 135	2	912758	912764
	3	912753	912764
140 145	2	912759	Ext. Up 912765
	3	912754	912765
150 155	2	912759	Ext. Down 912742
	3	912754	912742
160 165	2	912741	912766
	3	912754	912766
170 175	2	912760	912767
	3	912757	912767
160 165	2	912761	912769
	3	912758	912769
170 175	2	912762	912769
	3	912758	912769

**TABLE 3 — Seal Part Numbers & Dimensions**

Falk Part No.	Manufacturer's Part No. ★		Basic Dimensions – Inches		
	Chicago Rawhide	National	Shaft Dia	Outside Dia	Width †
912741	CRW 34886	...	3.500	4.505	.375
912742	CRWA 70080	477436	7.000	8.507	.500
912743	CRW 11123	...	1.125	1.628	.250
912745	CRW 12545	...	1.250	2.129	.250
912747	CRWA 15142	473228	1.500	2.506	.312
912749	CRWA 17285	471504	1.750	2.441	.312
912753	CRW 19992	...	2.000	3.005	.312
912754	CRW 22440	...	2.250	3.256	.375
912757	...	417316	2.750	3.756	.375
912758	CRW 29906	...	3.000	4.008	.375
912759	CRW 32393	...	3.250	4.254	.375
912760	CRW 39922	...	4.000	5.004	.375
912761	CRW 44959	...	4.500	5.506	.375
912762	CRWA 49985	476865	5.000	6.256	.500
912763	CRWA 54960	...	5.500	6.756	.500

**TABLE 3 — Seal Part Numbers & Dimensions (Continued from Column 1)**

Falk Part No.	Manufacturer's Part No. ★		Basic Dimensions – Inches		
	Chicago Rawhide	National	Shaft Dia.	Outside Dia	Width †
912764	CRWA 60016	...	6.000	7.506	.500
912765	CRWA 64993	...	6.500	7.506	.500
912766	CRWHA 72539	...	7.250	8.757	.625
912767	CRWH 77540	...	7.250	9.250	.625
912769	CRWHA 92536	...	9.250	11.258	.625
912770	CRWH 100051	...	10.000	12.008	.625
912771	CRWH 110051	...	11.000	13.008	.625

★ Subject to substitution of equivalent seals without notice.

† The seal listed may be slightly narrower than the width listed.