

Use the following steps to determine high and low speed seal type and part numbers:

1. Use Table 1 to determine V-ring seal part numbers and dimensions.
2. Refer to Table 3 for Falk oil seal part numbers. Use Table 2 to determine O-ring part numbers and dimensions. Use Table 4 to determine manufacturer's part numbers and dimensions for oil seals.

**TABLE 1 — LBXD & LBXQ Drywell V-Ring Seal Part Numbers & Dimensions**

DRIVE SIZE	Falk Part Number	Manufacturer's Part Number CR Industries	Basic Dimensions – Inches	
			Inside Diameter	Width
1100	2912858	402202	7.800	.410
1200	2913534	402500	8.860	.980
1300	2912448	402750	9.720	.980
1400	2912803	403250	11.500	.980
1500	2913172	403500	12.400	.980
1600	2917215	403750	13.270	.980
1750	2914611	404500	15.940	.980
1850	2918891	405000	17.720	.980

**TABLE 2 — "O" Ring Part Numbers & Dimensions**

Falk Part Number	Industry Part Number	Basic Dimensions – Inches		
		Inside Diameter	Outside Diameter	Width
926957	144	2.500	2.688	.0937
926968	152	3.250	3.438	.0937
926969	153	3.500	3.688	.0937
926996	458	14.500	15.000	.2500
927080	451	11.000	11.500	.2500
927084	455	13.000	13.500	.2500
927112	245	4.375	4.625	.1250
2912848	378	10.500	10.875	.1875
2913171	464	17.500	18.000	.2500
927116	249	4.875	5.125	.1250
927121	254	5.500	5.750	.1250
926995	466	18.500	19.000	.2500
2918389	470	21.000	21.500	.2500
2918890	471	22.000	22.500	.2500

**TABLE 3 — Falk Oil Seal Part Numbers**

DRIVE SIZE	Location & Seal Type	H.S. Shaft (All Types)		L.S. Shaft (All Reductions)			
		Triple	Quad	LBXU	LBXD	LBXQ Upper	LBXQ Lower
1100	Outer-Lip	913018	913010	912816	912816	912816	912816
	Inner-Lip	...	913011	912833	912767	912833	912767
	Inner Bush & "O" Ring	3200208	...	...	...	...	...
	Drywell "O" Ring	926957	...	...	...	...	...
		...	...	...	2912848	...	2912848
1200	Outer-Lip	912993	913018	2913531	912767	2913531	912767
	Inner-Lip	...	912946	912767	912827	912767	912827
	Inner Bush & "O" Ring	3200211	...	...	...	...	...
	Drywell "O" Ring	926968	...	...	...	...	...
		...	...	...	927080	...	927080
1300	Outer-Lip	912993	913018	912672	912578	912672	912578
	Inner-Lip	...	912946	912578	912580	912578	912580
	Inner Bush & "O" Ring	3200211	...	...	...	...	...
	Drywell "O" Ring	926968	...	...	...	...	...
		...	...	...	927084	...	927084
1400	Outer-Lip	913030	912993	912580	912580	912580	912580
	Inner-Lip	...	912994	912940	912550	912940	912550
	Inner Bush & "O" Ring	3200336	...	...	...	...	...
	Drywell "O" Ring	926969	...	...	...	...	...
		...	...	...	926996	...	926996
1500	Outer-Lip	912995	912993	912550	912550	912550	912550
	Inner-Lip	...	912994	2913168	912808	2913168	912808
	Inner Bush & "O" Ring	3200213	...	...	...	...	...
	Drywell "O" Ring	927112	...	...	...	...	...
		...	...	...	2913171	...	2913171
1600	Outer Lip	913028	913030	912809	912809	912809	912809
	Inner Lip	...	...	2913977	912905	2913977	912905
	Inner Bush & "O" Ring	3200332	3200336	...	...	...	...
	Drywell "O" Ring	927116	926969	...	...	...	...
		...	...	...	926995	...	926995
1750	Outer Lip	913028	913030	2900932	2900932	2900932	2900932
	Inner Lip	...	...	2913542	912842	2913542	912842
	Inner Bush & "O" Ring	3200332	3200336	...	...	...	...
	Drywell "O" Ring	927116	926969	...	...	...	...
		...	...	...	2918389	...	2918389
1850	Outer Lip	913014	913028	912902	912903	912902	912903
	Inner Lip	...	...	912903	2918744	912903	2918744
	Inner Bush & "O" Ring	3200215	3200332	...	...	...	...
	Drywell "O" Ring	927121	927116	...	...	...	...
		...	...	...	2918890	...	2918890

**TABLE 4 — Seal Part Numbers & Dimensions**

Falk Part Number	Manufacturer's Part Number ★			Basic Dimensions — Inches		
	CR Industries	Johns-Manville	National	Shaft Diameter	Outside Diameter	Width †
912550	CRWH1-115021	9019LUP	...	11.500	13.008	.750
912578	...	16554LUP	455476	9.000	10.260	.750
912580	...	9830LUP	455270	10.000	11.010	.750
912672	CRWH1-90006	11552LUP	...	9.000	10.008	.750
912767	CRWH1-77540	...	...	7.750	9.258	.625
912808	HDS1-1300570	10093LUP	...	13.000	15.008	.938
912809	CRW1-122580	...	...	12.250	13.821	.719
912816	CRWH1-70016	10063LPD	455517	7.000	8.007	.750
912827	CRWH1-85009	10371LUP	455489	8.500	10.008	.750
912833	CRWH1-70052	11577LUP	455084	7.000	8.507	.750
912842	HDS1-1550250	10516LUP	...	15.500	17.008	.750
912902	HDS1-1500240	...	...	15.000	16.508	.688
912903	HDS1-1500380	...	...	15.000	16.758	.750
912905	HDS1-1375240	...	...	13.750	15.258	.688
912940	...	17846LDS	417020	10.000	12.008	.625
912946	CRW1-17558 (V)	4465LPD H5/L16 (V)	...	1.750	2.754	.375
912993	CRWH1-24914 (V)	9790LUP H5/L16 (V)	450519V	2.500	3.256	.500
912994	CRWH1-24984 (V)	10208LUP H5/L16 (V)	...	2.500	3.505	.438
912995	CRWH1-34892 (V)	11197LUP H5/L16 (V)	...	3.500	4.506	.500
913010	CRW1-14861 (V)	11654LUP H5/L16 (V)	...	1.500	2.004	.313
913011	CRW1-14940 (V)	12184LUP H5/L16 (V)	481507V	1.500	2.254	.375
913014	CRWH1-44973 (V)	9170LUP H5/L16(V)	455200V	4.500	5.506	.562
913018	CRW1-17379 (V)	14849LPD H5/L16 (V)	...	1.750	2.506	.313
913028	CRWH1-37405 (V)	7146LUP H5/L16(V)	...	3.750	4.756	.500
913030	...	14042LPD H5/L16(V)	...	2.750	3.500	.375
2900932	HDS1-1350250	...	...	13.500	15.008	.750
2913168	CRWH1-115041	...	...	11.500	13.508	.750
2913531	CRSH1-77530	...	...	7.750	9.007	.650
2913542	HDS2-1350542	...	...	13.500	15.508	.750
2913977	HDS2-1225525	...	...	12.250	14.258	.640
2918744	HDS2-1625243	...	...	16.250	17.758	.688

★ Subject to substitution of equivalent seals without notice. Manufacturer's part numbers ending in V or (V) denote high temperature seals.

† Seal listed may be slightly narrower than the width listed.