

**Falk Seal Part Numbers**

UNIT SIZE	No. of Reductions		H.S. Shaft Seal Part No. All Type F	L.S. Shaft — Seal Part Number		
	Concentric Shaft Units	Right Angle Shaft Units		Types FC and FZ	Types FCB and FZB	
					Extension	Inner
1020	2	3	912743	912853	912616	912676
	3	4	912743	912853	912616	912676
1030	2	3	912743	912749	912778	912860
	3	4	912746	912749	912778	912860
	4	5	912743	912749	912778	912860
1040	2	3	912746	912775	912913	912861
	3	4	912746	912775	912913	912861
	4	5	912743	912775	912913	912861
1050	2	3	912749	912781	912777	912546
	3	4	912749	912781	912777	912546
	4	5	912743	912781	912777	912546
1060	2	3	912805	912757	912759★	912857
	3	4	912849	912757	912759★	912857
	4	5	912746	912757	912759★	912857
1070	2	3	912835	912759	912536★	912832
	3	4	912749	912759	912536★	912832
	4	5	912746	912759	912536★	912832
1080	2	3	912781	912741	912791	912816
	3	4	912845	912741	912791	912816
	4	5	912849	912741	912791	912816
1090	2	3	912781	912850	912787	912834
	3	4	912845	912850	912787	912834
	4	5	912849	912850	912787	912834
1100	2	3	912758	912761	912762	912856
	3	4	912754	912761	912762	912856
	4	5	912845	912761	912762	912856
1110	2	...	912741	912762	...	...
	3	...	912754	912762	...	...
	4	...	912775	912762	...	...
1120	2	...	912741	912763	...	...
	3	...	912680	912763	...	...
	4	...	912775	912763	...	...
1130	2	...	912536	912764	...	...
	3	...	912680	912764	...	...
	4	...	912775	912764	...	...

★ Seal numbers listed are for Single Ended Standard Rotation. For Single Ended Opposite Standard Rotation and Double Ended Gear Side Extension seal number is 912758 for Size 1060 and 912741 for Size 1070.

**Seal Part Numbers and Dimensions**

Falk Part Number	Manufacturers' Part No.†		Basic Dimensions — Inches		
	Chicago Rawhide	National	Shaft Diameter	Outside Diameter	Width‡
912536	CRWA 37389	...	3.750	4.756	.375
912546	CRWH 47394	455138	4.750	5.756	.562
912590	CRWH 58716	455075	5.875	7.131	.625
912616	CRWA 16085	473231	1.625	2.378	.312
912666	CRWH 62535	455109	6.250	7.756	.750
912676	CRWH 27368	457316	2.750	3.756	.500
912680	CRWA 25075	476273	2.500	3.628	.375
912741	CRWA 34887	477437	3.500	4.505	.375
912743	CRW11123	471652	1.125	1.628	.250
912746	CRWA 13650	471192	1.375	2.129	.312
912749	CRWA 17285	471504	1.750	2.441	.312
912754	CRW22440	472636	2.250	3.256	.375
912757	...	417316	2.750	3.756	.375
912758	CRWA 29907	475995	3.000	4.008	.375
912759	CRWA 32395	476470	3.250	4.254	.375
912761	CRWA 44960	...	4.500	5.506	.375
912762	CRWA 49985	476865	5.000	6.256	.500
912763	CRWA 54960	...	5.500	6.756	.500
912764	CRWA 60016	...	6.000	7.506	.500
912775	...	470898	2.125	2.879	.375
912777	CRWA 28669	477344	2.875	3.756	.375
912778	CRWA 22354	471272	2.250	3.005	.375
912781	CRWA 26238	475458	2.625	3.628	.375
912787	CRWA 47395	415138	4.750	5.756	.500
912791	CRWA 42419	...	4.250	5.256	.375
912805	CRWA 23702	472856	2.375	3.355	.438
912816	CRWH 70016	455517	7.000	8.009	.750
912832	CRWH 64994	455294	6.500	7.508	.562
912834	CRWH 78738	455121	7.875	9.383	.750
912835	CRWA 29866	...	3.000	3.756	.375
912845	CRWA 19832	472492	2.000	2.754	.312
912849	CRWA 16062	473230	1.625	2.256	.375
912850	CRWA 40077	...	4.000	5.631	.375
912853	CRWA 14939	470625	1.500	2.254	.312
912856	HDS1590408	...	8.750	10.008	.625
912857	CRWH 52488	455645	5.250	6.507	.625
912860	...	455389	3.625	4.504	.468
912861	CRWH 42426	455195	4.250	5.256	.468
912913	CRWA 24898	471271	2.500	3.256	.375

† Subject to substitution of equivalent seals without notice.

‡ The seal listed may be slightly narrower than the width listed.