



Why Choose Rexnord?

When it comes to providing highly engineered products that improve productivity and efficiency for industrial applications worldwide, Rexnord is the most reliable in the industry. Our commitment to customer satisfaction and superior value extends to every area of our business.

Delivering Lowest Total Cost of Ownership

The highest quality products are designed to help prevent equipment downtime, increase productivity and deliver dependable operation.

Valuable Expertise

An extensive product offering is accompanied by global sales specialists, customer service and maintenance support teams, available anytime.

Solutions to Enhance Ease of Doing Business

Our commitment to operational excellence means you benefit from getting the right products to the right place at the right time.

Why Choose Link-Belt Mounted Ball Bearings?

Technical Expertise

Link-Belt® ball bearings are supported by a team of highly experienced application engineers to provide customers with bearing performance analysis and proper bearing selection for optimal application performance.

Innovative Attachment Options

Replacing ball bearings on your equipment should be straight-forward and error-free, so we have developed patented shaft attachment options to improve shaft holding force and simplify installation. The Centrik-Lok™ CL and Shurlok mounting collars provide industry leading shaft grip strength for extended life in high vibration environments such as package and material handling.

Leading Seal Options

Link-Belt ball bearings offer highly engineered sealing options for a wide range of applications and industries. Our range of seal options allows for the proper balance of protection against contaminants and dynamic bearing performance to reduce premature bearing failure, reduce unplanned downtime and improve overall productivity.

Range of Duty

Link-Belt mounted ball bearings offer the widest range of duty and performance options. We offer a wide variety of housings, seals and mounting options to provide customers with a broad range of product configurations. Combined with our vast component supermarket, Rexnord is able to provide the optimal ball bearing tailored to the specific needs of your application.

Availability

We understand that equipment downtime is not an option for our customers. Rexnord utilizes a network of warehouses and distribution channels to provide inventory coverage for our product offering and provide greater customer satisfaction.





Wide Range of Duty Options

Heavy-Duty



- Shaft sizes up to 4" (102 mm)
- Set screw, eccentric and SHURLOK adapter-mount shaft attachments
- Alignable, precision, deep-groove ball bearings



Intermediate-, Standard- and Medium-Duty



- Shaft sizes up to 4" (102 mm)
- Centrik-Lok, set screw and eccentric cam locking collars
- Narrow or wide inner rings
- Light and heavy contact seals



Corrosion-Resistant



- Shaft sizes up to 1-15/16" (49 mm)
- Stainless steel bearing insert
- Front and rear double lip seals
- Protective safety caps

Process & Motion Control Products & Solutions For Your Business

- Bearing
- Coupling
- Gear
- Industrial Chain
- Conveying Equipment
- FlatTop
- Product Services

Industries Served

- Aggregates
- Air Handling
- Construction Machinery
- Food & Beverage
- Forest Products
- Material Handling
- Mining
- Pumps & Compressors
- Steel

