



Bearing Technical Support
Email:
 bearing.tech.support@rexnord.com
Phone:
 (317) 273-5781

Link-Belt Ball Bearings

The Largest Product Scope in the Power Transmission Industry

Rexnord has recently consolidated the Link-Belt® and MB® product lines to form the largest ball bearing product scope in the power transmission industry. The consolidation is a result of years of listening to our customers request a single-brand identity.

Spring 2014 marked the end of the MB brand which has been fully transitioned under Link-Belt nomenclature. Customers that enjoyed the quality and special features of MB can still enjoy them today under our Link-Belt brand. Link-Belt Ball Bearings can be found in heavy-to light-duty applications such as aggregates, mining, package handling, air and fluid handling and food and beverage.

We have a dedicated team of application engineers located at our Indianapolis, IN (USA) manufacturing facility that bring more than 100 years of industry experience. Our application engineering expertise in combination with dedicated Account Executives has positioned Rexnord to provide Industry-leading support.

Easy reference for you

As you become more familiar with our products and nomenclature we encourage you to download our *Bearing Mobile Pro™* app. The app can be located on both iTunes for iOS devices and Google Play for Android devices. The app provides installation instructions, dimensions, videos, and much more. We understand interchanging products can be a daunting task; Rexnord strives to make it easier for our distributors and customers.

Link-Belt Ball Bearing Scope

	Class			
	Intermediate	Standard	Medium	Heavy
Set-Screw	✓	✓	✓	✓
Eccentric	✓	✓		✓
Centrik-Lok®		✓	✓	
Adaptor Mount				✓
Shurlok®				✓
Shaft Size	1/2" 2 15/16"	1/2" 4"	1" 3 1/2"	3/4" 3 15/16"

The most common interchanges are listed below for quick reference. These are not all encompassing as to what can be interchanged. If you cannot find an interchange please refer to our Bearing Mobile Pro app for the full interchange guide or contact our application engineering team for assistance.

Introducing the Rexnord Bearing MobilePro™ app for iOS and Android devices.

Download the app on iTunes for iOS devices.
Download the app on Google Play for Android devices.

Medium Duty Ball Bearings — Centrik Lok

Bore	Housing	SealMaster	Browning	Dodge	Link-Belt
1"		MSFT16T	VF2B-316	F2B-DLM-100	MFCL216N
1 3/16"		MSFT19T	VF2B-319	F2B-DLM-103	MFCL219N
1 7/16"	2 Bolt Flange	MSFT23T	VF2B-323	F2B-DLM-107	MFCL223N
1 11/16"		MSFT27T	VF2B-327	F2B-DLM-111	MFCL227N
1 3/4"		MSFT28T	VF2B-328	F2B-DLM-112	MFCL228N
1 15/16"		MSFT31T	VF2B-331	F2B-DLM-115	MFCL231N
1"		MSF16T	VF4B-316	F4B-DLM-100	MFCL216N
1 3/16"		MSF19T	VF4B-319	F4B-DLM-103	MFCL219N
1 7/16"		MSF23T	VF4B-323	F4B-DLM-107	MFCL223N
1 11/16"		MSF27T	VF4B-327	F4B-DLM-111	MFCL227N
1 3/4"		MSF28T	VF4B-328	F4B-DLM-112	MFCL228N
1 15/16"	4 Bolt Flange	MSF31T	VF4B-331	F4B-DLM-115	MFCL231N
2 3/16"		MSF35T	VF4B-335	F4B-DLM-203	MFCL235N
2 7/16"		MSF39T		F4B-DLM-207	MFCL239N
2 11/16"		MSF43T		F4B-DLM-211	MFCL243N
2 15/16"		MSF47T		F4B-DLM-215	MFCL247N
3 3/16"		MSF51T		F4B-DLM-303	MFCL251N
3 7/16"		MSF55T		F4B-DLM-307	MFCL255N
1"		MP16T	VPB-316	P2B-DLM-100	MPCL216N
1 3/16"		MP19T	VPB-319	P2B-DLM-103	MPCL219N
1 7/16"		MP23T	VPB-323	P2B-DLM-107	MPCL223N
1 11/16"		MP27T	VPB-327	P2B-DLM-111	MPCL227N
1 3/4"		MP28T	VPB-328	P2B-DLM-112	MPCL228N
1 15/16"	Pillow Block	MP31T	VPB-331	P2B-DLM-115	MPCL231N
2 3/16"		MP35T	VPB-335	P2B-DLM-203	MPCL235N
2 7/16"		MP39T		P2B-DLM-207	MPCL239N
2 11/16"		MP43T		P2B-DLM-211	MPCL243N
2 15/16"		MP47T		P2B-DLM-215	MPCL247N
3 3/16"		MP51T		P2B-DLM-303	MPCL251N
3 7/16"		MP55T		P2B-DLM-307	MPCL255N
1 3/16"		MFC19T	VFCB-319	FC-DLM-103	MFCCL219N
1 7/16"		MFC23T	VFCB-323	FC-DLM-107	MFCCL223N
1 11/16"		MFC27T	VFCB-327	FC-DLM-111	MFCCL227N
1 3/4"		MFC28T	VFCB-328	FC-DLM-112	MFCCL228N
1 15/16"		MFC31T	VFCB-331	FC-DLM-115	MFCCL231N
2 3/16"	Piloted Flange	MFC35T	VFCB-335	FC-DLM-203	MFCCL235N
2 7/16"		MFC39T		FC-DLM-207	MFCCL239N
2 11/16"		MFC43T		FC-DLM-211	MFCCL243N
2 15/16"		MFC47T		FC-DLM-215	MFCCL247N
3 3/16"		MFC51T		FC-DLM-303	MFCCL251N
3 7/16"		MFC55T		FC-DLM-307	MFCCL255N

Medium Duty Ball Bearings — Set Screw

Bore	Housing	SealMaster	Timken	Dodge	Link-Belt
1"		MSFT16	YCJTM 1	F2B-SCM-100	MFXS216N
1 3/16"		MSFT19	YCJTM 1 3/16	F2B-SCM-103	MFXS219N
1 7/16"	2 Bolt Flange	MSFT23	YCJTM 1 7/16	F2B-SCM-107	MFXS223N
1 11/16"		MSFT27	YCJTM 1 11/16	F2B-SCM-111	MFXS227N
1 3/4"		MSFT28	YCJTM1 3/4	F2B-SCM-112	MFXS228N
1 15/16"		MSFT31	YCJTM 1 15/16	F2B-SCM-115	MFXS231N
1"		MSF16	YCJM 1	F4B-SCM-100	MFS216N
1 3/16"		MSF19	YCJM 1 3/16	F4B-SCM-103	MFS219N
1 7/16"		MSF23	YCJM 1 7/16	F4B-SCM-107	MFS223N
1 11/16"		MSF27	YCJM 1 11/16	F4B-SCM-111	MFS227N
1 3/4"		MSF28	YCJM 1 3/4	F4B-SCM-112	MFS228N
1 15/16"	4 Bolt Flange	MSF31	YCJM 1 15/16	F4B-SCM-115	MFS231N
2 3/16"		MSF35	YCJM 2 3/16	F4B-SCM-203	MFS235N
2 7/16"		MSF39	YCJM 2 7/16	F4B-SCM-207	MFS239N
2 11/16"		MSF43	YCJM 2 11/16	F4B-SCM-211	MFS243N
2 15/16"		MSF47	YCJM 2 15/16	F4B-SCM-215	MFS247N
3 3/16"		MSF51		F4B-SCM-303	MFS251N
3 7/16"		MSF55		F4B-SCM-307	MFS255N
1"		MP16	YASM 1	P2B-SCM-100	MPS216N
1 3/16"		MP19	YASM 1 3/16	P2B-SCM-103	MPS219N
1 7/16"		MP23	YASM 1 7/16	P2B-SCM-107	MPS223N
1 11/16"		MP27	YASM 1 11/16	P2B-SCM-111	MPS227N
1 3/4"		MP28	YASM 1 3/4	P2B-SCM-112	MPS228N
1 15/16"	Pillow Block	MP31	YASM 1 15/16	P2B-SCM-115	MPS231N
2 3/16"		MP35	YASM 2 3/16	P2B-SCM-203	MPS235N
2 7/16"		MP39	YASM 2 7/16	P2B-SCM-207	MPS239N
2 11/16"		MP43	YASM 2 11/16	P2B-SCM-211	MPS243N
2 15/16"		MP47	YASM 2 15/16	P2B-SCM-215	MPS247N
3 3/16"		MP51		P2B-SCM-303	MPS251N
3 7/16"		MP55		P2B-SCM-307	MPS255N
1 3/16"		MFC19	RFC 1 3/16	FC-SCM-103	MFCS219N
1 7/16"		MFC23	RFC 1 7/16	FC-SCM-107	MFCS223N
1 11/16"		MFC27	RFC 1 11/16	FC-SCM-111	MFCS227N
1 3/4"		MFC28	RFC 1 3/4	FC-SCM-112	MFCS228N
1 15/16"		MFC31	RFC 1 15/16	FC-SCM-115	MFCS231N
2 3/16"	Piloted Flange	MFC35	RFC 2 3/16	FC-SCM-203	MFCS235N
2 7/16"		MFC39		FC-SCM-207	MFCS239N
2 11/16"		MFC43		FC-SCM-211	MFCS243N
2 15/16"		MFC47		FC-SCM-215	MFCS247N
3 3/16"		MFC51		FC-SCM-303	MFCS251N
3 7/16"		MFC55		FC-SCM-307	MFCS255N