



Please contact your Rexnord Representative with any questions:

**Rexnord FlatTop Europe**  
Einsteinstraat 1, 2691 GV 's-Gravanzande  
The Netherlands  
Phone: +31 174 445 111  
After Hours Emergency  
Phone: +31 174 445 112  
(including countries not listed)

**Rexnord FlatTop Italy**  
Phone: +39 0522 639333

**Rexnord FlatTop Germany**  
Phone: 0800 588 8083

**Rexnord FlatTop France**  
Phone: 0805 540 444

**Rexnord FlatTop India**  
Phone: +91 98813 99026

**Rexnord FlatTop China**  
Phone: +86 21 66188307

**Rexnord FlatTop North America**  
1272 Dakota Drive  
Grafton, WI, 53024 USA  
Phone: 1-262-376-4700

[www.rexnord.com](http://www.rexnord.com)  
[www.rexnordflattop.com](http://www.rexnordflattop.com)

## Rexnord 2755 Series TableTop Chains Heavy Load Chain (BSM) Material

Rexnord FlatTop continuously develops and introduces new products for conveyors meeting increased performance demands of bottling line efficiency along with sustainability targeting safety, water and energy reduction.

### Designed for Heavy Load Side-Flex Applications

The 2755 Series Chain is designed for heavy load side-flex applications which require a combination of high-strength and robustness.

### Special Formulated Material

BSM material is a specially formulated acetal with self lubricating additives ensuring low-friction consistently, resulting in long service life.

### Large Carrying Surface

The large carrying surface offers optimal product stability in single-track conveyors.

### Multiple Applications

- Returnable crates
- Keg handling



BSM 2755



BSM 2755

**Robust Design**

- Makes the chain suitable for heavy load applications

**BSM Material**

- Provides constant low-friction in combination with high wear resistance



**Large Carrying Surface**

- The 7.87 inch (200 mm) width of the links provides a large carrying surface to offer optimal product stability in single track conveyors

**High Working Load**

- Capabilities offer the possibility to build longer conveyors to reduce the required number of drive motors

Chain Type	Code Number	Plate Width	Weight	Working Load (max)	Side-flex Radius	Backflex Radius	Plate Thickness
		in / mm			kg / m	N	in / mm
BSM 2755	774.17.31	7.87 / 200	6.1	12.500	23.9 / 600	4.9 / 125	0.45 / 11.5

Standard length: 1.52 m – 5 ft (19 links)

