



Please contact your Rexnord Representative with any questions:

**Rexnord FlatTop Europe**  
Einsteinstraat 1, 2691 GV  
's-Gravenzande  
The Netherlands  
Phone: +31 174 445 111  
After Hours Emergency  
Phone: +31 174 445 112  
(including countries not listed)

**Rexnord FlatTop Italy**  
Phone: +39 0522 639333

**Rexnord FlatTop Germany**  
Phone: 0800 588 8083

**Rexnord FlatTop France**  
Phone: 0805 540 444

**Rexnord FlatTop India**  
Phone: +91 040 23078243

**Rexnord FlatTop China**  
Phone: +86 21 52436100

**Rexnord FlatTop  
North America**  
1272 Dakota Drive  
Grafton, WI, 53024 USA  
Phone: 1-262-376-4700

[www.rexnord.com](http://www.rexnord.com)  
[www.rexnordflattop.com](http://www.rexnordflattop.com)

## Rexnord NSH 1500 MatTop Sprockets Molded Hygienic Split Design

Rexnord FlatTop continuously develops and introduces new products for conveyors. Our product lines are frequently reviewed to ensure they continue to provide high-performance and overall value to customers.

### Rexnord NSH 1500 MatTop Sprockets

The design of the molded Rexnord 1500 MatTop® Sprockets has been improved. The sprockets combine a more hygienic design with quicker installation and are available in 24-tooth and 32-tooth executions.

### Quick installation

The sprocket can be mounted over the shaft using two connecting bolts instead of four. This translates into direct savings in installation time and costs.

### Compatibility

The Rexnord NSH 1500 MatTop Sprockets are designed to offer optimal engagement with all Rexnord 1500 Series MatTop executions, including versions with Double Positrack® Tracking Guides.

### Price and availability

This product offering provides a competitive, economical alternative to machined sprockets. Please contact your Rexnord sales representative for more details on the total cost of ownership value and pricing information.





Sprocket Type	Code Number	Number of Teeth	Hub Width A	Shaft Size B	Width C	Pitch Diameter D	Outside Diameter E	Equivalent of KUS1500
			in / mm	in / mm	in / mm	in / mm	in / mm	
<b>Split molded sprocket NSH 1500 with 24 teeth</b>								
NSH1500-24T_30MM_1KW	10378150	24	1.57 / 40	1.18 / 30	0.75 / 19	4.52 / 114.9	4.55 / 115.5	10131508
NSH1500-24T_40MM_1KW	10378415	24	1.57 / 40	1.57 / 40	0.75 / 19	4.52 / 114.9	4.55 / 115.5	10131510
<b>Split molded sprocket NSH 1500 with 32 teeth</b>								
NSH1500-32T_30MM_1KW	10378419	32	1.57 / 40	1.18 / 30	0.75 / 19	6.04 / 153.4	6.09 / 154.8	10331547
NSH1500-32T_40MM_1KW	10378423	32	1.57 / 40	1.57 / 40	0.75 / 19	6.04 / 153.4	6.09 / 154.8	10332257

