



① **AirMax Desiccant Breathers**

The AirMax® Plus™ AM-HG includes a desiccant material that absorbs water and protects against moisture intrusion. It includes a color indicator system for easy replacement identification. In addition to the desiccant and particulate filtration, the AM-HG has an expansion chamber that isolates lubricants from all levels of ambient humidity and a check valve to ensure no excess pressure/vacuum builds.

② **Oil Sample Port**

Allows easy oil sampling for predictive/preventive maintenance procedures. Predictive maintenance of oil can prolong the life of your gear unit.

③ **Quick Disconnect Oil Inlet and Outlet**

Allows for easy connection to mobile oil filtration device if oil sampling indicates that the oil contains contaminants.

④ **Oil Site Glass with Anti-foam Block**

Allows you to easily verify the correct oil level while the gear drive is running. Ensuring the oil level is correct protects the gearing from overheating and unnecessary wear.

⑤ **Ball Drain Valve**

Provides a fast and efficient way to drain oil when it is time for routine maintenance.

⑥ **Sealed Dipstick**


Allows you to verify the unit has the correct oil level while the gear drive is not in operation. Ensuring the oil level is correct protects gearing from overheating and unnecessary wear.

Falk Reliability Package for Falk V-Class, Quadrive and UltraMax Gear Drives


Prevent Downtime. Lower Costs. Increase Operational Reliability.

You know predictive maintenance prevents downtime, lowers costs and increases operational reliability. The Falk® Reliability Package helps with all these goals as you maintain Falk V-Class™ Gear Drives, Falk


Quadrive Shaft Mounts and Falk UltraMax® Concentric Drives. A proven success among Rexnord customers, this industry-leading standardized package includes options that simplify preventive work and greatly increase efficiency. For more information, ask your Rexnord Account Executive.



Falk V-Class



UltraMax



Quadrive

For A6 mounting only, as shown