



**Bearing Reference Numbers (Manufacturers Numbers on Page 2)**

**DOUBLE REDUCTION**

**TRIPLE REDUCTION**
**TABLE 1 — Bearing Reference & Part Numbers**

DRIVE SIZE	1AB2-50	1AB2-51	1AB3-50	1AB3-51	3A3-70	3A3-71	4A1	4A2	5A1	5A2
<b>2070</b>	921528	921584 <sup>8</sup>	921570	921573 <sup>8</sup>	921393	921393	921389	921447	921352	921352
<b>2080</b>	921734	921572 <sup>8</sup>	921570	921573 <sup>8</sup>	921393	921393	921494	921529	921310	921758
<b>2090</b>	921734 <sup>1</sup>	921572 <sup>8</sup>	921434 <sup>9</sup>	921578 <sup>8</sup>	921388	921583	921567	921567	921414	921414
<b>2100</b>	921531 <sup>2</sup>	921579 <sup>8</sup>	921434 <sup>9</sup>	921578 <sup>8</sup>	921388	921372 <sup>11</sup>	921551	921551	921436	921422
<b>2110</b>	921531 <sup>2</sup>	921579 <sup>8</sup>	921528 <sup>10</sup>	921584 <sup>8</sup>	921556	921324	921448	921448	921422	921422 <sup>15</sup>
<b>2120</b>	921580	921611 <sup>8</sup>	921528 <sup>10</sup>	921584 <sup>8</sup>	921574	921574	921412 <sup>12</sup>	921459 <sup>12, 14</sup>	921311	921311
<b>2130</b>	921542	921589 <sup>8</sup>	921734 <sup>1</sup>	921572 <sup>8</sup>	921588	921588	921332 <sup>13</sup>	921332 <sup>13</sup>	921417	921417 <sup>16</sup>
<b>2135</b>										
<b>2140</b>	921541 <sup>3</sup>	921608 <sup>8</sup>	921734 <sup>1</sup>	921572 <sup>8</sup>	921448	921448	921463	921463	921464	921464
<b>2145</b>										
<b>2150</b>	921436 <sup>4</sup>	921617 <sup>8</sup>	921531 <sup>2</sup>	921579 <sup>8</sup>	921482	921482	921646	921646	921416	921416
<b>2155</b>										
<b>2160</b>	921470 <sup>5</sup>	921610 <sup>8</sup>	921531 <sup>2</sup>	921579 <sup>8</sup>	921482	921482	921480	921480	921475	921475
<b>2165</b>										
<b>2170</b>	921653 <sup>6</sup>	921651 <sup>8</sup>	921580	921611 <sup>8</sup>	921482	921482	921481	921481	921475	921475
<b>2175</b>										
<b>2180</b>	921653 <sup>6</sup>	921831 <sup>8</sup>	921542	921589 <sup>8</sup>	921470	921470	921625	921625	921794	921794
<b>2185</b>										
<b>2190</b>	921912	921651 <sup>7 &amp; 8</sup>	921541 <sup>3</sup>	921608 <sup>8</sup>	921422	921422	921625	921625	921916	921917
<b>2195</b>										

<sup>1</sup> Use 921556 for drives with bevel gear ratio 4.13 (Refer to Eng. 267-112).

<sup>2</sup> Use 921489 for drives with bevel gear ratio 4.13 (Refer to Eng. 261-112).

<sup>3</sup> Use 921486 for drives with bevel gear ratio 4.13 (Refer to Eng. 261-112).

<sup>4</sup> Use 921306 for drives with bevel gear ratio 4.13 (Refer to Eng. 267-112).

<sup>5</sup> Use 921463 for drives with bevel gear ratio 4.13 (Refer to Eng. 267-112).

<sup>6</sup> Use 921652 for drives with bevel gear ratio 4.13 (Refer to Eng. 267-112).

<sup>7</sup> Use 921914 for drives with bevel gear ratio 4.13 (Refer to Eng. 267-112).

<sup>8</sup> This double row tapered roller bearing has spacer built to specific clearance specifications and MUST be replaced as a complete assembly. The component parts of these bearings are not interchangeable.

<sup>9</sup> Use 921526 for drives with bevel gear ratio 4.13 (Refer to Eng. 267-112).

<sup>10</sup> Use 921561 for drives with bevel gear ratio 4.13 (Refer to Eng. 267-112).

<sup>11</sup> Use 921388 for ratios 63.82 thru 78.16 and 95.73 thru 194.6.

<sup>12</sup> Use 921542 for triple reduction drives.

<sup>13</sup> Use 921413 for triple reduction drives.

<sup>14</sup> Use 921413 for double reduction drives with ratios 5.06 thru 6.20, 28.36 and 31.39.

<sup>15</sup> Use 921311 for Type YBXD drives.

<sup>16</sup> Use 921305 for Type YBXD drives.



**TABLE 2 — Bearing Cross Reference Numbers <sup>1</sup>**

Falk Part No.	Manufacturer's Number
<b>TAPERED ROLLER BEARINGS</b>	
921305	94700/94113
921306	95475/95925
921310	861/854
921311	99600/99100
921324	635/632
921332	HH923649/HH923610
921352	6580/6535
921372	569/563
921388	65200/65500
921389	6280/6220
921393	59175/59412
921412	943/932
921413	941/932
921414	938/932
921416	93800/93125
921417	94649/94113
921422	99550/99100
921434	HM807049/HM807010
921436	95500/95925
921447	65212/65500
921448	HH221431/HH221410
921459	HH224335/HH224310
921463	HH228340/HH228310
921464	93750/93125
921470	HH228349/HH228310
921475	EE126097/126150
921480	HH234031/HH234010
921481	HH234048/HH234010
921482	HH224334/HH224310
921486	HH224332/HH224310
921489	6576/6535
921494	H715336/H715311
921526	HM807046/HM807010
921528	HM813841/HM813811
921529	H715345/H715311
921531	6559C/6535
921541	HH224346/HH224310
921542	HH221434/HH221410
921551	HH221430/HH221410
921556	H715332/H715311
921561	HM813840/HM813811
921567	HH814547/HH814510
921570	HM803149/HM803111
921572	565-90016
921573	25580-90091
921574	6455/6420
921578	33890-90076
921579	659-90033
921580	6559C/6536
921583	HM813836/HM813811
921584	33225-90091
921588	835/832
921589	759-90169
921608	866-90088
921610	95491-90132
921611	749A-90040
921617	67388-90019
921625	HH840249/HH840210
921646	HH231649/HH231610
921651	99550-90014
921652	EE450551/451212
921653	EE450577/451212
921734	H715341/H715311
921758	JHM522649/JHM522610
921794	H852849/H852810
921831	EE107057-90065
921912	HH234018/HH234048
921914	94649/94118D
	X3S94650(.010 BEP)
921916	EE722110/722185
921917	EE724119/724195

<sup>1</sup> Rexnord suppliers of bearings are: Tapered Roller Bearings – Timken, Bower & Tyson.