



# PRODUCT INFO SHEET

## REXNORD® KLEANTOP® ACTIVE DRIVE™ 1.33" LINK BELT

ADAPTABLE BELTING FOR SPIRAL  
CAGE SYSTEMS



### REXNORD KLEANTOP ACTIVE DRIVE LINK 1.33" SPECIFICATIONS

Belt Type	1.33"		
Pitch	1.33" (33.78 mm)		
Mesh Sizes	0.86" x 1.33" (nominal on outer edges) 3" x 1.33" (nominal in the belts interior) Variable openings available		
Belt Width	16" to 56" (406.4 mm to 1,422 mm)		
Rods	0.188" (4.78 mm) diameter		
Materials	WRSS/T304 Stainless Steel/T316 Stainless Steel)		
Flat Strip	.5" x 0.060" (12.7 x 1.52 mm)		
Turn Ratio		Inside Bar	Outside Bar
Reduced	1.60 - 1.99	26102-2 = 1	26102-2 = 2
Standard	2.0 - 2.39	26102-1 = 2	26102-1 = 2
Oversized	2.4 - 2.80	26102-2 = 2	26102-2 = 2
Welds	Button head welds on rods		
Inner Edge Construction	Coned shaped extended button head		
Maximum Belt Edge Tension	300 lbs.		
Extended Rebars	Available		
Lane Dividers	Available		

### KEY INDUSTRIES

- Meat and Poultry
- Baking and Snack
- Fruit and Vegetable
- Ready-to-eat

### APPLICATIONS

- Freezing
- Cooling
- Proofing
- Drying

### SPROCKET INFORMATION

Number of Teeth	Overall Diameter		Pitch Diameter		Hub Dia. (Bottom Dia.)		Bore Size		Face Width		Approximate Weight	
	in	mm	in	mm	in	mm	in	mm	in	mm	lbs.	kg
For 1.33" pitch belts												
14T	6.3	161.0	5.9	152.2	5.3	135.1	0.937 - 2.5	2.379 - 63.5	2.0	50.8	1.80	0.82

### Motion Control Solutions Regal Rexnord

Contact us: [rexnord.com/contact](https://www.rexnord.com/contact)

[regalrexnord.com](https://www.regalrexnord.com)

The proper selection and application of products and components, including assuring that the product is safe for its intended use, are the responsibility of the customer. To view our Application Considerations, please visit <https://www.regalrexnord.com/Application-Considerations>. To view our Standard Terms and Conditions of Sale, please visit <https://www.regalrexnord.com/Terms-and-Conditions-of-Sale> (which may redirect to other website locations based on product family).

"Regal Rexnord" is not indicative of legal entity. Refer to product purchase documentation for the applicable legal entity. Regal Rexnord, Rexnord and KleanTop are trademarks of Regal Rexnord Corporation or one of its affiliated companies. © 2022 Regal Rexnord Corporation, All Rights Reserved. MCSSP22124E • Form# 10530E

