


REXNORD® KLEANTOP® ACTIVE DRIVE™ GRID BELT

ADAPTABLE BELTING FOR SPIRAL
CAGE SYSTEMS



REXNORD KLEANTOP ACTIVE DRIVE GRID SPECIFICATIONS

Belt Type	1"	1.2"
Pitch	1.08" (27.43 mm)	1.2" (30.48 mm)
Belt Width <i>Heavy Duty</i>	12" to 60" 305 to 1,219 mm	12" to 60" 305 to 1,219 mm
Link <i>Heavy Duty</i>	.5" x .105" 12.7 mm to 2.7 mm	.5" x .090" 12.7 mm to 2.3 mm
Rods	0.188" (4.77 mm)	0.188" (4.77 mm)
Materials	T304 stainless steel throughout rods and mesh, also available in T316 stainless steel. All mesh overlays are constructed with spring temper stainless steel.	
Wire Gauge	0.058" (1.47 mm)	
Inner Edge Construction	Coned shaped extended button head	
Turn Ratio <i>Standard</i>	2.2 - 2.5	2.0 - 2.5
<i>Reduced</i>	1.6 - 2.1	1.6 - 1.99
Mesh Overlay	12 - 72	12 - 60
Welds	Single	Single
Combo Links	Available	1" (25.4 mm) only
Raised Spirals	Available	Available

KEY INDUSTRIES

- Meat and Poultry
- Baking and Snack
- Fruit and Vegetable
- Ready-to-eat

APPLICATIONS

- Freezing
- Cooling
- Proofing
- Drying

SPROCKET INFORMATION

Number of Teeth	Pitch Diameter		Root Diameter		Bore Size		Sprocket Thickness		Approximate Weight	
	in	mm	in	mm	in	mm	in	mm	lbs.	kg
For 1" pitch belts										
18T	6.2	157.7	5.6	142.2	1 - 4	25.4 - 101.6	2.0	50.8	1.60	0.73
For 1.2" pitch belts										
16T	6.2	156.2	5.4	137.3	1 - 4	25.4 - 101.6	2.0	50.8	1.60	0.73

Motion Control Solutions Regal Rexnord

Contact us: [rexnord.com/contact](https://www.rexnord.com/contact)

[regalrexnord.com](https://www.regalrexnord.com)

The proper selection and application of products and components, including assuring that the product is safe for its intended use, are the responsibility of the customer. To view our Application Considerations, please visit <https://www.regalrexnord.com/Application-Considerations>. To view our Standard Terms and Conditions of Sale, please visit <https://www.regalrexnord.com/Terms-and-Conditions-of-Sale> (which may redirect to other website locations based on product family).

"Regal Rexnord" is not indicative of legal entity. Refer to product purchase documentation for the applicable legal entity. Regal Rexnord, Rexnord and KleanTop are trademarks of Regal Rexnord Corporation or one of its affiliated companies. © 2022 Regal Rexnord Corporation, All Rights Reserved. MCSSP22126E • Form# 10532E