


Shims and gaskets are available in kit form only: order by "Kit Number." Use reference and part numbers for identifying parts when received. Disregard extra parts: this is a multipurpose kit.

| Reference Number | Description | Shim Thickness | DRIVE SIZE | | | | |
|------------------|---|----------------|------------|--------|--------|--------|--------|
| | | | 2 | 3 | 4 | 5 | 6 |
| | | | Kit Number | | | | |
| | | | 712329 | 712337 | 712339 | 712344 | 712349 |
| Part Numbers | | | | | | | |
| 5 | Gasket — High Speed Seal Triple and Quadruple Quintuple | ... | 143337 | 143338 | 143338 | 126146 | 126146 |
| | | ... | 128103 | 127678 | 127678 | 127755 | 127755 |
| 19 | Shim — Low Speed Bearing Plate | .002 | 125904 | 125904 | 125904 | 125905 | 125906 |
| | | .005 | 704714 | 704714 | 704714 | 704716 | 704718 |
| | | .010 | 704715 | 704715 | 704715 | 704717 | 704719 |
| 24 | Gasket — Low Speed Head | ... | 211990 | 211991 | 211992 | 211993 | 211994 |
| 24A | Shim — Low Speed Head | .005 | 216043 | 216206 | 215998 | 216067 | 216087 |
| | | .010 | 704743 | 704746 | 704742 | 704744 | 704745 |
| 41 | Shim — Intermediate Thrust Plate | .002 | ... | ... | ... | ... | 126612 |
| | | .005 | ... | ... | ... | ... | 704793 |
| | | .010 | ... | ... | ... | ... | 704794 |
| 56 | Gasket — Low Speed Seal Cage | ... | 134224 | 133891 | 134128 | 134236 | 134346 |
| 62 | Shim — Low Speed End Cover | .005 | 134226 | 133893 | 134130 | 134238 | 133993 |
| | | .015 | 704723 | 704720 | 704722 | 704724 | 704721 |
| 63 | Gasket — Low Speed End Cover | .007 | 164930 | 163906 | 163907 | 163908 | 163909 |
| | | .009 | 704738 | 704728 | 704730 | 704732 | 704734 |
| | | .012 | 704739 | 704729 | 704731 | 704733 | 704735 |
| 5AB-8 | Shim — Bevel Pinion | .005 | 141233 | 141234 | 141235 | 141593 | 141237 |
| | | .002 | ... | ... | ... | 705067 | ... |
| 7AB-6 | Gasket — Bevel Gear | ... | 134225 | 133894 | 134129 | 134237 | 134347 |



| Reference Number | Description | Shim Thickness | DRIVE SIZE | |
|------------------|----------------------------------|--|---|---|
| | | | 7 | 75 |
| | | | Kit Number | |
| | | | 712355 | 712356 |
| | | | Part Number | |
| 5 | Gasket — High Speed Seal Cage | ... | 221310 ★ | 221310 ★ |
| 19 | Shim — Low Speed Bearing Plate | .002 .005 .010 | 221315 704747 704748 | 221315 704747 704748 |
| 24 | Gasket — Low Speed Head | ... | 221313 | 221313 |
| 24A | Shim — Low Speed Head | .005 .010 | 223272 704749 | 223272 704749 |
| 56 | Gasket — Low Speed Seal Cage | ... | 146258 | ... |
| 62 | Shim — Low Speed Seal Cage | .005 .015 704727007009015031 | 146259 704727 | 1119431 710153 710154 710155 |
| 63 | Gasket — Low Speed End Cover | .007 .009 .012 | 163910 704736 704737 | |
| 76 | Shim — Intermediate Thrust Plate | .002 .005 .010 | 146097 704725 704726 | 146097 704725 704726 |
| 82 | Gasket — High Speed Head | ... | 221312 | 221312 |
| 5AB-8 | Shim — Bevel Pinion | .005 | 146453 | ... |
| 7AB-6 | Gasket — Low Speed Baffle | ... | 146256 | ... |

★ For 7CB3 model C, 7EB3 model C with backstop, and the 75CB3 model A, use in addition shims 269079, 705226, and 705227 under the high speed seal cage.