

Rexnord Tollok Locking Assemblies Interchange Guide

REXNORD TOLLOK™	CLAMPEX	RINGFEDER / ECOLOC	AMERIDRIVES	CLIMAX	RINGSPANN	TSUBAKI	FENNER B-LOC	STUWE	BIKON
TLK110	KTR 250	RfN 7110	-	C170	RLK 110	PL TF	B 800	-	8000
TLK130	KTR 200	7004	-	-	RLK 130	-	-	-	7000.A
TLK131	KTR 201	7007	-	-	RLK 131	-	-	-	7000.B
TLK132	KTR 203	RfN 7013.0 / 7003	3003	C123	RLK 132	PL FL	B 103	-	1003
TLK133	KTR 206	RfN 7013.1 / 7006	3006	C133	RLK 133	PL AE	B 106	-	1006
TLK134	KTR 225	-	-	-	-	-	-	-	1506
TLK138	-	-	-	C193	-	PL KE	B 109	-	-
TLK139	-	-	-	-	-	-	-	-	4500
TLK200	KTR 100	RfN 7012	3020	C200	RLK 200	PL AS	B 400	-	4000
TLK250	KTR 125	-	-	-	RLK 250	-	-	-	5500 SP
TLK250L	KTR 125.1	-	-	-	RLK 250L	-	-	-	5500 S
TLK300	KTR 150	RfN 8006	-	-	RLK 300	PL EL	B 500	-	5000
TLK350	KTR 105	7061	-	-	RLK 350	-	-	-	-
TLK400	-	-	-	-	-	PL AD	-	-	-
TLK401	-	RfN 7015.1	-	-	-	-	-	-	-
TLK401,0	-	RfN 7015.0	-	-	-	-	-	-	-
TLK450/452	KTR 400	7005	3012	C405	RLK 402	-	B 112	-	DOB. 1012
TLK451	KTR 401	7515	3015.1	-	RLK 404 light	-	-	-	DOB. 1015.1
TLK451.0	-	-	3015	C415	RLK 404	-	B115.0	-	DOB. 1015.0
TLK500	KTR 700	-	-	C600	-	-	WK	-	9500
TLK601	-	RfN 4051	3051	-	-	-	SD 20	SD - 51	1029/51
TLK602	-	RfN 4091	3091	C732	-	-	SD 30	SD - 91	1029/91
TLK603	KTR 603	RfN 4071-4061	3071	C733	RLK 603	PL SL	SD 10	SD - 71/72	1029/71
TLK622	KTR 620	-	3171	-	RLK 606	-	-	HSD - 22	-
TLK623	-	-	3191	-	-	-	-	HSD - 23	-
TLK681	-	RfN 4161-4181	3181	-	RLK 608	-	-	HSD - 81	1007
TLK683	-	-	3193	-	-	-	-	HSD - 83	-