


Falk™ TRUE HOLD® Low Speed Backstops — Never Let Safety Slip



Falk TRUE HOLD NRT Style

Anytime you're moving materials upgrade, you have the potential for trouble. Should the electrical power fail, a motor fail or someone trip the emergency cable, the results can be disastrous. . . for employees and equipment.

That's why operations the world over, rely on Falk TRUE HOLD Backstops and their instant-response, no-slip mechanism to help put a stop to trouble before it can start.

Size-for-size TRUE HOLD Backstops provide more system holding power than any other backstop. Plus, Long-life designs and our ability to engineer and manufacture complete, integrated drive packages, assure that you get the ideal system for your needs, whether it's a single, tandem or multiple backstop configuration.

Choose from Type NRTH for both low speed and semi-high speed applications and Type NRT for heavy-duty high torque applications.

Now, that's confidence... that's TRUE HOLD.

Long Lasting

The Falk NRT backstops are furnished with the best available lubrication and lubrication sealing system in the industry. Two double-lip seals on both sides of the backstop assure positive lube retention. The external seal grease purge feature combined with the Airmax breather prevent contamination of the generous oil supply from particulate matter and from moisture laden air.

Increased Life

The oversized, heavy-duty cylindrical rollers have a wide contact area and the rolling action minimizes wear and increases performance, life, and reliability.

No Slip

The instant response, fail safe roller/ramp stopping mechanism prevents reverse rotation and eliminates the potential for slippage, protecting man, machine, and your entire investment.

Available

Stock bore sizes available in 1 week or less with our premium breakdown service. (See reverse side.)



Stock Bore Size

NRT SIZE	Inch	Metric
1075	3.4375	100
1075	3.9375	
1085	4.4375	130
1085	4.9375	
1095	4.9375	150
1095	5.4375	
1105	5.9375	200
1105	6.4375	
1105	6.9375	
1115	6.9375	220
1115	7.4375	
1115	7.9375	
1115	8.000	
1115	8.4375	
1125	8.5000	240
1125	8.9375	
1125	9.0000	
1135	10.5000	260
1145		300
1155		350

The bore sizes listed above can ship from stock in one week. NRT is bored to suit with shipping lead time of one week.

Rexnord Experience

Rexnord Drives System Expertise

Assistance with proper selection for your specific application whether single, tandem, or multiple drives. For virtually any application where materials need to be moved up steep grades, including inclined conveyors, high angle conveyor, or bucket elevators used in mining, grain, power generation, cement, and aggregates. TRUE HOLD NRT backstops with torque rating to 747,000 ft-lb (1,012,185 Nm).



Factory Warranty* — We're so confident in the performance and reliability of these backstops that we're backing the fully featured NRT series with the best standard warranty in the business. Our full, 3-year Heavy-Duty Warranty provides "shaft-to-shaft protection on all Falk components — including bearings and seals (warranty extends for years from date of shipment). It's an industry first... and one more powerful reason why Rexnord is your ultimate bottom-line value.

★ NRT series are provided with one year warranty.



Also available in larger sizes, up to 20 inch/510 mm bores and 747,000 ft-lb/1,012,185 Nm torque capacities. See Selection Guide 561-110 or contact Rexnord for detailed availability.

WORLDWIDE CUSTOMER SERVICE

AUSTRALIA
Rexnord Australia Pty. Ltd.
Picton, New South Wales
Phone: 61-2-4677-3811
Fax: 61-2-4677-3812

BRAZIL
Rexnord Correntes Ltda.
Sao Leopoldo - RS
Phone: 55-51-579-8022
Fax: 55-51-579-8029

CANADA
Rexnord Canada Ltd.
Scarborough, Ontario
Phone: 1-416-297-6868
Fax: 1-416-297-6873

CHINA
Rexnord China
Shanghai, China
Phone: 86-21-62701942
Fax: 86-21-62701943

EUROPE
Rexnord NV/SA
Mechelen, Belgium
Phone: 32-15-443881
Fax: 32-15-443860

Rexnord Kette GmbH
Betzdorf, Germany
Phone: 49-2741-2840
Fax: 49-2741-284-385

LATIN AMERICA
Rexnord International
Milwaukee, Wisconsin
Phone: 1-414-643-2366
Fax: 1-414-643-3222
E-mail: international1@rexnord.com

MEXICO
Rexnord S.A. de C.V.
Queretaro, Qro.
Phone: 52-442-218-5000
Fax: 52-442-218-1090

SINGAPORE
Rexnord International, Inc.
Singapore City, Singapore
Phone: 65-6338-5622
Fax: 65-6338-5422

UNITED STATES
Customer Service
Phone: 1-866-Rexnord
(1-866-739-6673)
E-mail: rexnordcs(state)@rexnord.com
Example: rexnordcs(ohio)@rexnord.com

ALL COUNTRIES NOT LISTED ABOVE
Rexnord International
Milwaukee, Wisconsin
Phone: 1-414-643-2366
Fax: 1-414-643-3222
E-mail: international2@rexnord.com