

Rexnord® TableTop® and MatTop® Chains



Rexnord® 8505 RubberTop™ MatTop® Chain

Rexnord® WHF (White High Temperature Friction Top) 8505 RubberTop™ MatTop® Chain is the newest addition to our comprehensive line of high-strength, transfer-efficient case and material handling conveying chains designed specifically for incline, decline and metering applications. The new tapered high friction RubberTop design produces a more effective grip so that cases and boxes remain secure - even on steep inclines or declines.

Rexnord WHF 8505 RubberTop MatTop chain combines the highest working load of any $\frac{3}{4}$ inch pitch (19.1 mm) MatTop chain with the most efficient (1-1/8 inch (28.6 mm)) inline self-clearing Nose-over Bar Transfer technology available, making larger loads and longer runs possible, while eliminating or minimizing deadplates. Capable

of incline angles of up to 30°, Rexnord WHF 8505 (high friction) RubberTop™ MatTop chain maintains pack spacing and prevents pack skewing during conveyor transfers.


With optimized rubber-to-product contact, the new Rexnord WHF 8505 MatTop chain's durable, non-marking, high friction rubber pads are integrally molded into high strength, low friction links, for long wearing and impact resistant chain performance.

Rexnord's superior chain-sprocket interaction eliminates belt slippage and ensures superior tracking, even at high speeds. Rexnord 8500 sprockets can be positioned anywhere along the entire width of the chain to offer maximum flexibility in conveyor design or retrofit.



Features & Benefits

- Specifically designed for incline, decline, and metering applications in case and material handling
- High friction top surface with new tapered design for more effective gripping
- Can be used with 1-1/8 inch (28.6 mm) Dynamic Nose-over Bars for easy, efficient inline transfers.
- High working loads: WHF8505 920 lb/ft (13,426 N/m)
- Hold down tabs are available for tracking and return configurations
- Rubber is integrally molded into links for superior retention and wear life
- High performance pins available for higher speeds and increased life
- High speed capability with superior tracking
- Multiple sprocket material and sizes available: split or single piece thermoplastic (NS, KU); split cast stainless steel (SSS)

Rexnord® Hold down TAB



Rexnord® Dynamic Nose-Over Bar Transfer



Rexnord, TableTop and MatTop are registered trademarks, and RubberTop is a trademark of Rexnord Industries, LLC. All rights reserved.

WORLDWIDE CUSTOMER SERVICE

AUSTRALIA

Rexnord Australia Pty Ltd
Picton, New South Wales
Phone: 61-2-4677-3811
Fax: 61-2-4677-3812

BRAZIL

Rexnord Correntes Ltda.
Sao Leopoldo - RS
Phone: 55-51-579-8022
Fax: 55-51-579-8029

CANADA

Rexnord Canada Ltd.
Scarborough, Ontario
Phone: 1-416-297-6868
Fax: 1-416-297-6873

CHINA

Rexnord Conveyor Products
(Wuxi) Co. Ltd.
Shanghai
Phone: 86-21-62701942
Fax: 86-21-627019433

FLATTOP EUROPE

Rexnord FlatTop Europe b.v.
's-Gravenzande, The Netherlands
Phone: 31-174-445-111
Fax: 31-174-445-222

After Hours/Emergency Phone:
31-174-445-112

Rexnord Marbett®, S.r.l.
Correggio (RE), Italy
Phone: 39-0522-639333
Fax: 39-0522-637778

RMCC Deutschland Kette GmbH
Aßlar-Werdorf, Germany
Phone: 49-6443-83140
Fax: 49-6443-831420

Rexnord FlatTop France
Orly Cedex
Phone: 33-1-4173-4220
Fax: 33-1-4173-4229

MEXICO

Rexnord FlatTop
Toll-Free Phone: 001-888-808-7787
Fax: 1-262-376-4720

UNITED STATES

Customer Service
Phone: 1-866-REXNORD
(1-866-739-6673)
Fax: 1-614-675-1898
E-mail: rexnordcs(state)@rexnord.com
Example: rexnordcsohio@rexnord.com

Rexnord FlatTop North America
Grafton, Wisconsin
Phone: 1-262-376-4700
Fax: 1-262-376-4720

Rexnord International - Power Transmission
Milwaukee, Wisconsin
Phone: 1-414-643-2366
Fax: 1-414-643-3222
international2@rexnord.com

ALL COUNTRIES NOT LISTED

Rexnord FlatTop Europe b.v.
's-Gravenzande, The Netherlands
Phone: 31-174-445-111
Fax: 31-174-445-222

After Hours/Emergency Phone:
31-174-445-112