



Key Industries:

- Bakery
- Snack
- Fruit & Vegetable
- Poultry
- Red Meat
- Seafood

Key Applications:

- Receiving
- Washing & Draining
- Cutting & Dicing
- Infeeds & Outfeeds
- Freezing
- Packaging

Contact Information:

1-866-REXNORD (within U.S.)
+1-414-643-2366 (outside U.S.)


www.Rexnord.com

Reduce Downtime in General Conveying Applications with Direct Food Contact

When your operation needs a versatile plastic modular belt, the 2010 Series KleanTop® offers a solution. Designed with features that can accommodate a variety of product types, the 2010 Series KleanTop is a favorite amongst food processors for its durability, ease in cleaning and reliability in conveying on a wide range of applications.

To achieve strength, a conveyor belt's design often sacrifices areas that allow for thorough sanitation. The 2010 Series KleanTop features an open hinge design and strong Rexnord plastics, enabling you to save time in sanitation and convey heavier loads in applications such as receiving, washing and packaging.

2010 Series KleanTop Key Features & Benefits



Strong Carrying Surface
Enables conveyance of larger product volumes, increasing throughput.

Open Hinge Design
Gives optimal combination of access for sanitation and abrasion resistance.

Rod Retention Design
Requires only a screwdriver for assembly and disassembly. Keeps rod securely in place, reducing risk of product contamination.



2011 Nub Top



2015 Flat Top



2018 Perforated Top

Rexnord 2010 Series KleanTop Belt Information

Belt Type	Belt Material	Standard Rod Material	Temperature Range						Belt Strength		Approximate Weight	
			Fahrenheit			Celsius						
			min	max		min	max		lbs / ft	N/m	lbs/ft ²	kg/m ²
				dry	wet		dry	wet				
2011 Nub Top	BHT (PP)	Polypropylene	40	220	212	4	104	100	800	11,672	1.89	9.23
	BLT (PE)	Polyethylene	-100	80	80	-73	27	27	500	7,295	2.03	9.91
	WHT (PP)	Polypropylene	40	220	212	4	104	100	800	11,672	1.89	9.23
	WLT (PE)	Polyethylene	-100	80	80	-73	27	27	500	7,295	2.03	9.91
2015 Flat Top	BHT (PP)	Polypropylene	40	220	212	4	104	100	800	11,672	1.89	9.23
	BLT (PE)	Polyethylene	-100	80	80	-73	27	27	500	7,295	2.03	9.91
	FTR (PA)	Polyester	-80	220	NR	-62	104	NR	1,000	14,590	2.89	14.11
	WHT (PP)	Polypropylene	40	220	212	4	104	100	800	11,672	1.89	9.23
	WLT (PE)	Polyethylene	-100	80	80	-73	27	27	500	7,295	2.03	9.91
2016 Perforated Top	WSM (POM)	Polyester	-40	180	150	-40	82	66	1,000	14,590	2.89	14.11
	BHT (PP)	Polypropylene	40	220	212	4	104	100	800	11,672	1.89	9.23
	FTR (PA)	Polyester	-80	220	NR	-62	104	NR	1,000	14,590	2.89	14.11
	WHT (PP)	Polypropylene	40	220	212	4	104	100	800	11,672	1.89	9.23
	WLT (PE)	Polyethylene	-100	80	80	-73	27	27	500	7,295	2.03	9.91

Rexnord 2010 Series KleanTop KU2010 TruTrack Thermoplastic Sprocket Information

Number of Teeth		Pitch Diameter		Outside Diameter		Bore Diameter (Shaft Ready)								Bore Diameter (Idler)				Approximate Weight	
						Round				Square				in		mm			
						in	mm	in	mm	in	mm	in	mm	in	mm	in	mm	in	mm
						min	max	min	max	min	max	min	max	min	max	min	max	min	max
8	8	5.2	132.7	4.8	120.9	3/4	3	20	75	1 1/2	2	40	50	3/4	3	20	75	0.44	0.20
10	10	6.5	164.4	6.1	153.9	3/4	3 1/2	20	90	1 1/2	2 1/2	40	65	3/4	3 1/2	20	90	1.06	0.48
12	12	7.7	196.3	7.4	188	1	3 1/2	25	90	1 1/2	3 1/2	40	90	1	3 1/2	25	90	1.59	0.72
16	16	10.3	260.4	10.3	262.1	1	3 1/2	25	90	1 1/2	4 1/2	40	120	1	3 1/2	25	90	3.62	1.64