


# REXNORD® KLEANTOP® ACTIVE DRIVE™ 1" LINK BELT

ADAPTABLE BELTING FOR SPIRAL  
CAGE SYSTEMS



## REXNORD KLEANTOP ACTIVE DRIVE LINK 1" SPECIFICATIONS

Belt Type	1"
Pitch	1.08"
Mesh Sizes	.5" x 1" (12.7 x 25.4 mm) 1" x 1" (25.4 x 25.4 mm) Variable openings available
Mesh Size (inner/outer) Tight Radius (inner/outer)	.5" x 1"   .5" x 1.5" (12.7 x 25.4 mm)   12/7 x 38.1 mm 1" x 1"   1" x 1.5" (25.4 x 25.4   25.4 x 38.1 mm)
Belt width Standard Radius Tight Radius	12" to 60" (305 x 1,524 mm) 12" to 54" (305 x 1,372 mm)
Rods	Heavy Duty: 0.188" (4.77 mm) diameter
Materials	WRSS/T304 Stainless Steel/T316 Stainless Steel
Flat Strip	.5" x 0.060" (12.7 x 1.52 mm)
Turn Ratio Standard (Double bar inside) Reduced (Single bar inside) Reduced (No bar) Oversized (Not standard/special)	2.0 x belt width to 2.59 x belt width 1.7 x belt width to 1.99 x belt width 1.5 x belt width 1.69 x belt width 2.6 x belt width to 3.2 x belt width
2.85 Bar Available	
Welds	Button head welds on rods
Inner Edge Construction	Coned shaped extended button head
Maximum Belt Edge Tension	300 lbs.
Extended Rebars	Available
Lane Dividers	Available

## KEY INDUSTRIES

- Meat and Poultry
- Baking and Snack
- Fruit and Vegetable
- Ready-to-eat

## APPLICATIONS

- Freezing
- Cooling
- Proofing
- Drying

## SPROCKET INFORMATION

Number of Teeth	Pitch Diameter		Hub Dia. (Bottom Dia.)		Bore Size		Sprocket Thickness		Approximate Weight	
	in	mm	in	mm	in	mm	in	mm	lbs.	kg
For 1" pitch belts										
18T	6.1	155.4	5.6	142.7	1-4	25.4 - 101.6	2.0	50.8	1.60	0.73

## Motion Control Solutions Regal Rexnord

Contact us: [rexnord.com/contact](https://www.rexnord.com/contact)

[regalrexnord.com](https://www.regalrexnord.com)

The proper selection and application of products and components, including assuring that the product is safe for its intended use, are the responsibility of the customer. To view our Application Considerations, please visit <https://www.regalrexnord.com/Application-Considerations>. To view our Standard Terms and Conditions of Sale, please visit <https://www.regalrexnord.com/Terms-and-Conditions-of-Sale> (which may redirect to other website locations based on product family).

"Regal Rexnord" is not indicative of legal entity. Refer to product purchase documentation for the applicable legal entity. Regal Rexnord, Rexnord and KleanTop are trademarks of Regal Rexnord Corporation or one of its affiliated companies. © 2022 Regal Rexnord Corporation, All Rights Reserved. MCSSP22125E • Form# 10531E