




Rexnord 1040 Series Magnetflex TableTop Chain

FULL METAL PASTEURIZER BELT



MEETS INCREASING PERFORMANCE DEMANDS

Rexnord FlatTop continuously develops solution-oriented, innovative conveyor chain and components to meet the increasing performance demands of high-speed and mass-flow conveyors in the beverage and food industries. Our Rexnord® 1040 Series Magnetflex® TableTop® Chain provides a perfect option for side-flexing conveyors in lines where TableTop Chain is used.

IMPROVED CONTAINER HANDLING

Rexnord 1040 Series Magnetflex TableTop Chain offers excellent flatness to support even the most critical beverage container shapes and materials, such as PET bottles. The chain is available in two surface executions: table top (FTM) and flush grid (FGM), and in multiple Rexnord engineered plastics: XLG, PSX®, DRY-PT®, HP™ and DKA.

IMPROVED SAFETY

A patented pin retention solution improves worker safety. Pins can be inserted with low force, without the need for a hammer and punch. The pins are locked by clicking the links slightly backward. This makes chain installation and maintenance fast, safe and easy.

ENERGY SAVING

The chain weight of the 1040 Series is significantly lower, compared to similar chain designs in the market. This reduces the tension on the drive shaft, which translates into direct energy-saving opportunities.


COMPATIBILITY

The Rexnord 1040 Series Magnetflex TableTop Chain is compatible with the Rexnord 1050/1060 Series Magnetflex TableTop Chain and uses the same sprocket type.

The Rexnord 1040 Series Magnetflex TableTop Chain can be installed in an original industry standard conveyor setup without any modifications. The chain cannot be connected to the Rexnord 1050/1060 Series TableTop Chain.

Superior performance in dynamic, high-speed container conveying applications, including:

- High-speed, side-flexing single-track conveying applications
- Mass side-flexing conveying applications



XLG1040

DRY-PT1040

FEATURES AND BENEFITS

Excellent flatness

- The Rexnord 1040 Series Magnetflex TableTop Chain design offers excellent flatness to support even the most critical beverage containers

Maintenance

- The Rexnord 1040 Series Magnetflex TableTop Chain is very easy and fast to install, without the need for a hammer and punch. Simply insert the pin and bend the links backward to 'click' the pin in the secured position

Please contact your
Rexnord representative
with any questions:

Rexnord FlatTop Europe
Einsteinstraat 1, 2691 GV
's-Gravenzande
The Netherlands
Phone: +31 174 445 111
After Hours Emergency
Phone: +31 174 445 112

Rexnord FlatTop North America
Phone: 1-866-REXNORD

www.rexnord.com

Chain Type	Material	Code Number	Working Load (max)	Weight	Backflex Radius (min)	Plate Thickness	Sidelflex Radius (min)	Plate Width
			lbs/N	lbs/ft / kg/m	in/mm	in/mm	in/mm	in/mm


Rexnord 1040 Series Magnetflex Flat Top TableTop Chain Material Overview

DRY-PT1040FTM	DRY-PT	10604554	337/ 1500	0.67/ 1.00	5.12/ 130.0	0.34/ 8.7	19.7/ 500	3.33/ 83.8
PSX1040FTM	PSX	10604578						
XLG1040FTM	XLG	10604555						
HP1040FTM	HP	10608553						
DKA1040FTM	DKA	10608551						


Rexnord 1040 Series Magnetflex Flush Grid TableTop Chain Material Overview

DRY-PT1040FGM	DRY-PT	10604582	337/ 1500	0.64 / 0.95	5.12/ 130.0	0.34/ 8.7	19.7/ 500	3.33/ 83.8
PSX1040FGM	PSX	10604586						
XLG1040FGM	XLG	10604583						
HP1040FGM	HP	10608555						
DKA1040FGM	DKA	10608554						


Flush grid (35% open area) top view




Flat top (closed surface) top view



Front view



Side view



rexnord.com

866-REXNORD/866-739-6673 (Within the U.S.) or +1 414-643-2366 (Outside the U.S.)



OUR INNOVATION MOVES